

PROCEEDINGS OF SPIE

High-Power Diode Laser Technology XVII

Mark S. Zediker
Editor

3–5 February 2019
San Francisco, California, United States

Sponsored and Published by
SPIE

Volume 10900

Proceedings of SPIE 0277-786X, V. 10900

SPIE is an international society advancing an interdisciplinary approach to the science and application of light.

The papers in this volume were part of the technical conference cited on the cover and title page. Papers were selected and subject to review by the editors and conference program committee. Some conference presentations may not be available for publication. Additional papers and presentation recordings may be available online in the SPIE Digital Library at SPIDigitalLibrary.org.

The papers reflect the work and thoughts of the authors and are published herein as submitted. The publisher is not responsible for the validity of the information or for any outcomes resulting from reliance thereon.

Please use the following format to cite material from these proceedings:

Author(s), "Title of Paper," in *High-Power Diode Laser Technology XVII*, edited by Mark S. Zediker, Proceedings of SPIE Vol. 10900 (SPIE, Bellingham, WA, 2019) Seven-digit Article CID Number.

ISSN: 0277-786X
ISSN: 1996-756X (electronic)

ISBN: 9781510624429
ISBN: 9781510624436 (electronic)

Published by

SPIE

P.O. Box 10, Bellingham, Washington 98227-0010 USA
Telephone +1 360 676 3290 (Pacific Time) · Fax +1 360 647 1445
SPIE.org

Copyright © 2019, Society of Photo-Optical Instrumentation Engineers.

Copying of material in this book for internal or personal use, or for the internal or personal use of specific clients, beyond the fair use provisions granted by the U.S. Copyright Law is authorized by SPIE subject to payment of copying fees. The Transactional Reporting Service base fee for this volume is \$18.00 per article (or portion thereof), which should be paid directly to the Copyright Clearance Center (CCC), 222 Rosewood Drive, Danvers, MA 01923. Payment may also be made electronically through CCC Online at copyright.com. Other copying for republication, resale, advertising or promotion, or any form of systematic or multiple reproduction of any material in this book is prohibited except with permission in writing from the publisher. The CCC fee code is 0277-786X/19/\$18.00.

Printed in the United States of America by Curran Associates, Inc., under license from SPIE.

Publication of record for individual papers is online in the SPIE Digital Library.

SPIE. DIGITAL LIBRARY
SPIDigitalLibrary.org

Paper Numbering: *Proceedings of SPIE* follow an e-First publication model. A unique citation identifier (CID) number is assigned to each article at the time of publication. Utilization of CIDs allows articles to be fully citable as soon as they are published online, and connects the same identifier to all online and print versions of the publication. SPIE uses a seven-digit CID article numbering system structured as follows:

- The first five digits correspond to the SPIE volume number.
- The last two digits indicate publication order within the volume using a Base 36 numbering system employing both numerals and letters. These two-number sets start with 00, 01, 02, 03, 04, 05, 06, 07, 08, 09, 0A, 0B ... 0Z, followed by 10-1Z, 20-2Z, etc. The CID Number appears on each page of the manuscript.

Contents

v	<i>Authors</i>
vii	<i>Conference Committee</i>
ix	<i>Introduction</i>

HIGH POWER VISIBLE LASER TECHNOLOGY

10900 04	500 watt blue laser system for welding applications [10900-2]
10900 05	1000 W blue fiber-coupled diode-laser emitting at 450 nm [10900-3]
10900 06	High brightness fiber coupled diode lasers at 450 nm [10900-4]
10900 09	High-power-class QCW red laser bars and stacks for pump and direct application [10900-7]
10900 0A	Development of BLUE IMPACT, a 450nm-wavelength light source for laser processing [10900-8]

HIGH POWER DEVICES I

10900 0C	Towards 300 W high power laser bars [10900-9]
10900 0D	976nm high brightness fiber-coupled laser modules for ytterbium fiber laser pumping [10900-10]
10900 0F	Enhanced power conversion efficiency in 900-nm range single emitter broad stripe laser diodes maintaining high power operability [10900-12]
10900 0G	Highly efficient high-power pumps for QCW fiber lasers [10900-13]
10900 0H	High brightness diodes and 600W and 60% efficient low SWaP fiber-coupled package enabled by reduced-mode (REM) diodes [10900-14]

HIGH POWER DEVICES II

10900 0I	High yield, highly manufacturable high-power wavelength stabilized DBR diode laser [10900-15]
10900 0J	Ultra-short pulse NIR and SWIR laser diode illuminators for automotive LiDAR [10900-16]

- 10900 OK **Development of highly efficient laser diodes emitting around 1060nm for medical and industrial applications** [10900-17]
- 10900 OL **940nm high-power laser diode based on AlGaAs/InGaAs GRIN-SCH and asymmetric structure** [10900-18]
- 10900 OM **Current spreading suppression by O- and Si-implantation in high power broad area diode lasers** [10900-19]
- 10900 OO **Recent progress in brightness scaling by coherent beam combining of tapered amplifiers for efficient high power frequency doubling** [10900-21]

DIODE RELIABILITY: JOINT SESSION WITH 10899 AND 10890

- 10900 OP **Physics of failure based reliability model of high-power InGaAs-AlGaAs strained QW lasers** [10900-22]
- 10900 OQ **A comparative analysis of the catastrophic degradation of AlGaAs/GaAs and AlGaAs/InGaAs laser diodes: role of the strained QWs** [10900-23]
- 10900 OR **Reduced facet temperature in semiconductor lasers using electrically pumped windows** [10900-24]
- 10900 OS **Impact of external optical feedback on high-power diode laser lifetime and failure modes** [10900-25]

DIODE PACKAGING: JOINT SESSION WITH 10899 AND 10890

- 10900 OT **Experimental and theoretical analysis of the effect of packaging induced thermal stress on high-power laser diode arrays** [10900-26]
- 10900 OU **Increased coupling efficiency of fiber coupled modules by smile compensation** [10900-27]
- 10900 OV **Offline development of active-alignment-algorithms by efficient interpolation of discrete databases** [10900-28]